

0.6 OD M67 x 0.75, Machine Vision Absorptive ND Filter



Stock #21-462 3-5 DAYS

- 1 +

A\$169.60

ADD TO CART

Qty 1-9
A\$169.60
Qty 10+
A\$162.88
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
0.6

Clear Aperture CA (mm):
62.50

Filter Thread:
M67 x0.75

Substrate: ☐
ND Filter Glass

Surface Quality: 40-20
Transmission (%): 25.00
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 6.0
Mount Thickness Including Threads (mm): 8.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
