

0.7 OD, 12.5mm Dia., IR Neutral Density Filter



Infrared (IR) Neutral Density (ND) Filters

Stock **#12-006** 3-5 DAYS

- 1 + **A\$328.00**

ADD TO CART

Qty 1-10
A\$328.00
Qty 11+
A\$295.20
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm): 12.50 ±0.2
Optical Density OD (Average): 0.7
Substrate: ☐ Germanium (Ge)
Coating:

Metallic Based ND
Surface Quality: 80-50
Thickness (mm): 1.00 ±0.2
Transmission (%): 20.0
Transmission Tolerance (%): ±2.0
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 2000 - 14,000
Parallelism (arcmin): <10
Clear Aperture (%): 90
Wavelength Range (µm): 2 - 14
Surface Flatness (P-V): 3 - 5λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant