

TECHSPEC[®] 0° AOI, 35.0mm Square, Hot Mirror



TECHSPEC High Performance Hot Mirrors

Stock #64-459 3-5 DAYS

-

1

+

A\$110.40

ADD TO CART

Qty 1-9

A\$110.40

Qty 10+

A\$96.48

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle of Incidence (°):

0

Coating:

Hot Mirror, 0°

Substrate: ☐

[BOROFLOAT[®]](#)

Dimensions (mm):

35.0 x 35.0
Surface Quality: 80-50
Thickness (mm): 3.30
Thickness Tolerance (mm): ±0.2
Type: Shortpass Filter
Dimensional Tolerance (mm): +0.0/-0.2
Coating Specification: T _{avg} >90% @ 400 - 690nm, R _{avg} >95% @ 710 - 1150nm AR: R _{avg} <1% @ 400 - 700nm
Wavelength Range (nm): 400 - 1150
Surface Flatness (P-V): 4 - 6λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant