

[See all 11 Products in Family](#)

## 1" Max. Opening, Soft Jaw Pliers



Stock #73-583 **4 In Stock**

1  A\$48<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$48.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Physical & Mechanical Properties

Tip to Tip Distance, Open (mm):  
25.4 (1")

### Regulatory Compliance

Certificate of Conformance:  
[View](#)

## Product Details

- Non-Marring Cushioned Tips
- Screw-In Cushioned Tip Design
- Replacement Tips Available

The slip joint design utilized in these pliers is ideal for handling optics, camera-lens assemblies, and other delicate components. Jaw openings range from 1" to 2.75" (dependent on model). Jaws feature screw-in plastic cushions to protect fine knurling and delicate finishes. Tool body is laminated and handles are covered with rolled vinyl to ensure proper grip.

---