

TECHSPEC® 10" Diameter x 100" FL Uncoated, Parabolic Mirror



Stock **#35-726-000** 3-5 DAYS

⊖ 1 ⊕ **A\$3,315.20**

ADD TO CART

Qty 1-2
A\$3,315.20
Qty 3+
A\$2,817.60
Volume Pricing
Request Quote

Get Product Downloads

Substrate: □
BOROFLOAT®

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 10.00 +0.06/-0
Diameter (mm): 254.00 +1.5/-0
Effective Focal Length EFL (inches): 100.0
Effective Focal Length EFL (mm): 2,540.00
Radius of Curvature (mm): 5,080.00
Aperture (f/#): f/10
Coating: Uncoated
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 229
Edge Thickness ET (inches): 1.75
Edge Thickness ET (mm): 44.50
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View