

TECHSPEC[®] 10" Diameter x 60" FL Uncoated, Parabolic Mirror



Stock #32-274-000 3-5 DAYS

-

1

+

A\$3,315.20

ADD TO CART

Qty 1-2
A\$3,315.20
Qty 3+
A\$2,817.60
Volume Pricing
Request Quote

Get Product Downloads

Substrate:

[BOROFLOAT[®]](#)[SUPREMAX[®]](#)

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 10.0 +0.06/-0
Diameter (mm): 254.00 +1.5/-0
Effective Focal Length EFL (inches): 60.0
Effective Focal Length EFL (mm): 1,524.00
Radius of Curvature (mm): 3,048.00
Aperture (f/#): f/6
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Clear Aperture CA (mm): 229
Edge Thickness ET (inches): 1.75
Edge Thickness ET (mm): 44.50
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View