

10", Green 530nm, Medium Intensity Linear Backlights

See More by [Advanced Illumination](#)



Advanced Illumination Medium Intensity Linear Backlights

Stock **#18-642** 3-5 DAYS

⊖ 1 ⊕

A\$1,502.40

ADD TO CART

Qty 1+

A\$1,502.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Color:
Green

Input Voltage (V):
24V

Model Number:
BL31310-530IC

Operating Temperature (°C):
0 - 50

Dimensions (mm):

267.2 x 32.2 x 21.7
Wavelength (nm): 530.00
Weight (g): 286
LED Lifetime (hours): 50000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Active Area (mm): 255.2 x 25
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Backlight
Illumination Mode: Constant
Environmental Rating: IP50
Minimum Input Current: 0.8A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)