

10 LED, White Adjustable LED Bar Light



Stock **#34-877** 3-5 DAYS

- 1 + **A\$1,176.00**

ADD TO CART

Qty 1+
A\$1,176.00

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color: White
Connector: M12, 5 pins
Input Voltage (V): 24VDC

Model Number: EFFI-FLEX-10-000
Mount: 2 Rails (1 for M6 T-Nuts)
Operating Temperature (°C): -10 to 50
Dimensions (mm): 235.0 x 51.0 x 49.0
Power Supply: Power Supply Required and Sold Separately. USA: #15-874 Europe: #15-875 Japan: #15-874 Korea: #15-874 China: #15-874
Number of LEDs: 10.00
Type of Illumination: LED Illuminator
Geometry: Line Light
Illumination Mode: Strobed or Constant
Environmental Rating: IP40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
