

10 lp/mm, 1" x 3", Fused Silica, Ronchi Ruling



Stock #57-884 CLEARANCE 5 In Stock

A\$553⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	A\$553.60 each
Qty 5+	A\$526.72 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Length (inches):
3.00

Pattern Size (mm):
12.7 x 25.4

Thickness (mm):
1.10

Width (inches):
1.00

Optical Properties

Vacuum Deposited Chrome **Coating:**

10.00 **Frequency (lp/mm):**

[Fused Silica](#) (Coming 7980) **Substrate:**

3.00 **Optical Density OD (Average):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.
