

10 lp/mm, 1" x 3", Fused Silica, Ronchi Ruling



Stock #57-884 CLEARANCE 5 In Stock

-

1

+

A\$553^{.60}

ADD TO CART

Volume Pricing	
Qty 1-4	A\$553.60 each
Qty 5+	A\$526.72 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
3.00	Length (inches):
12.7 x25.4	Pattern Size (mm):
1.10	Thickness (mm):
1.00	Width (inches):
Optical Properties	

Vacuum Deposited Chrome	Coating:
10.00	Frequency (lp/mm):
Fused Silica (Corning 7980)	Substrate:
3.00	Optical Density OD (Average):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.