

10 lp/mm 1" x 3", Opal Glass Ronchi Ruling Slide



Stock #59-545 3-5 DAYS

-

1

+

A\$408.00

ADD TO CART

Qty 1-4

A\$408.00

Qty 5+

A\$388.48

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating:
Vacuum Deposited Chrome

Dimensional Tolerance (inches):
±0.100

Frequency (lp/mm):
10.00

Substrate:
Opal Glass

Length (mm): 25.40
Optical Density OD (Average): >3.0
Pattern Size (mm): 12.7 x 25.4
Surface Quality: 40-20
Thickness (mm): 1.52 ±0.100
Width (mm): 76.20
Note: Pattern Location is Centered
NIST Certification: No
Line Width Tolerance (µm): ±0.002

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant