

TECHSPEC® 1.0 OD 50mm Diameter UV-VIS ND Filter



Stock #62-666 3-5 DAYS

-

1

+

A\$323.20

ADD TO CART

Qty 1-5
A\$323.20
Qty 6+
A\$258.56
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 +0.00/-0.20

Optical Density OD (Average):
1.0

Substrate:

Fused Silica (Corning 7980)

Coating:

Metallic Based ND
Surface Quality: 40-20
Thickness (mm): 5.00
Thickness Tolerance (mm): ±0.10
Transmission (%): 10.00
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 250 - 700
Clear Aperture (%): 80.00
Transmitted Wavefront, P-V: λ/4
Optical Density Tolerance (%): ±10
Parallelism (arcsec): <5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant