


TECHSPEC® 10 x 10mm, 0.44 Numerical Aperture, Uncoated, Square Precision Aspheric Lens



Stock #17-310 3-5 DAYS

- 1 + **A\$432.00**

ADD TO CART

Qty 1-5
A\$432.00
Qty 6+
A\$345.60
Volume Pricing
Request Quote

Get Product Downloads



Dimensions (mm):
10.00 x 10.00

Effective Focal Length EFL (mm):
11.25 @ 587.6nm

Numerical Aperture NA:
0.44

Back Focal Length BFL (mm):

5.71
Substrate: N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <1
Surface Quality: 40-20
Clear Aperture CA (mm): 9.00 x9.00
Edge Thickness ET (mm): 8.59
Center Thickness CT (mm): 10.02 ±0.10
f/#: 1.13
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 390 - 2500
Conjugate Distance: Infinite
Power (diopters): 88.89

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View