

10 x 60° Diffusing Angle 25mm Dia Mounted



Stock #48-009 3-5 DAYS

-

1

+

A\$288.00

ADD TO CART

Qty 1-5

A\$288.00

Qty 6+

A\$244.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle Tolerance (°):
±1 x±6

Diffusing Angle (°):
10 x60 (FWHM)

Clear Aperture CA (mm):
21.6

Diameter (mm):
25.00 ±0.1

Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 2.60
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Construction: Mounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant