

100 x 100mm Left-Handed Circular Polarizing Film (CP42HE)



Stock **#88-087** CLEARANCE 3-5 DAYS

-

1

+

A\$55.92

ADD TO CART

Qty 1+
A\$55.92

Volume Pricing
Request Quote

Get Product Downloads

Substrate:

[Polymer Film CP42HE](#)

Length (mm):

100.00

Operating Temperature (°C):

-40 to +80

Dimensions (mm):

100.0 x 100.0

Thickness (mm):

0.27 ±0.04

Transmission (%) : 42.00
Type : Left-Handed Circular Polarizer
Dimensional Tolerance (mm) : +0.0/-1.0
Construction : Polarizing Film
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.90
Heat Resistance (°C x Hours) : 80 x 500
Width (mm) : 100.00
#Sorting : 22.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Contains SVHC(s)