


1000nm, 25.4mm Dia., Colored Glass Replacement Longpass Filter



Colored Glass Replacement Longpass Filters

Stock **#15-463** [CONTACT US](#)

- 1 +

A\$84.80

ADD TO CART

Qty 1-10

A\$84.80

Qty 11+

A\$76.32

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.40 ±0.127

Optical Density OD (Average):
≥5.0

Cut-On Wavelength (nm):
1,000.00 ±9

Substrate: ☐

[BOROFLOAT®](#)

Operating Temperature (°C):
-100 to +400

Coating:
Dielectric

Index of Refraction n_d :
1.76

Rejection Wavelength (nm):
200 - 860

Surface Quality:
80-50

Thickness (mm):
1.10 ±0.10

Transmission (%):
>90 (typical)

Transmission Wavelength (nm):
1035 - 2500

Type:
Longpass Filter

Clear Aperture (%):
90

Environmental Durability:
MIL-STD-810, Method 507.3, Procedure III, Modified to 40 cycles

Physical Durability:
MIL-C-48497

Wavelength Range (nm):
200 - 2500

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 219:
[Compliant](#)

Certificate of Conformance:
[View](#)