

100mm Dia x 12.5mm FL Cold Mirror Coated, Parabolic Reflector



Stock **#90-967** [CONTACT US](#)

- 1 + **A\$776.00**

ADD TO CART

Qty 1-10
A\$776.00
Qty 11+
A\$682.40
Volume Pricing
Request Quote

Get Product Downloads

Substrate: [BOROFLOAT®](#)

Diameter (mm):
100.00 +0.0/-0.5

Focal Length FL (mm):
12.50

Aperture (f#):
0.125

Coating: Cold Mirror, 0°
Coating Type: Metal
Center Hole Diameter (mm): No Center Hole
Height (mm): 45.0
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
