

100mm Dia x 150mm Focal Length, MgF₂ Coated, PCX Condenser Lens



Stock #19-904 3-5 DAYS

-

1

+

A\$307.20

ADD TO CART

Qty 1-10
A\$307.20
Qty 11+
A\$275.20
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
100.00 +0.0/-0.5

Effective Focal Length EFL (mm):
150.00 @587.6nm

Back Focal Length BFL (mm):
136.16

Coating:
MgF₂ (400-700nm)

Coating Specification: R_{avg} ≤1.75% @400 - 700nm
Substrate: N-BK7
Surface Quality: 120-80
Center Thickness CT (mm): 21.00
Edge Thickness ET (mm): 2.72
Radius R₁ (mm): 77.52
Clear Aperture CA (mm): 95
f#: 1.5
Numerical Aperture NA: 0.33
Type: Condenser Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
