

100mm Dia x 400mm Focal Length, PCX Condenser Lens



Stock #27-503 3-5 DAYS

-

1

+

A\$132.80

ADD TO CART

Qty 1-10
A\$132.80
Qty 11+
A\$116.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
100.00 +0.0/-0.5

Effective Focal Length EFL (mm):
400.00 @587.6nm

Back Focal Length BFL (mm):
393.00

Coating:
Uncoated

Substrate: N-BK7
Surface Quality: 120-80
Center Thickness CT (mm): 10.00
Edge Thickness ET (mm): 3.86
Radius R₁ (mm): 206.70
Clear Aperture CA (mm): 97
f/#: 4.00
Numerical Aperture NA: 0.13
Type: Condenser Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View