

75mm Max. Aperture, Stainless Steel Iris Diaphragm



Stock #62-652 3-5 DAYS

- 1 + **A\$464.00**

ADD TO CART

Qty 1-4
A\$464.00
Qty 5+
A\$409.92
Volume Pricing
Request Quote

Get Product Downloads

Type: Unmounted
Minimum Aperture (mm): 5.5
Maximum Aperture (mm): 75.0
Outer Diameter (mm): 100.0

Construction: Blackened Aluminum Housing, Stainless Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 14.20
Number of Leaves: 20.00
Thickness (mm): 9.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)