

TECHSPEC® 100mm Length, T-Mount Extension Tube



Stock #52-296 **20+ In Stock**

⊖ 1 ⊕ A\$100⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	A\$100.00 each
Qty 5-9	A\$89.28 each
Qty 10-25	A\$83.04 each
Need More?	Request Quote

Product Downloads

General

Extension Tube **Type:**

Extension Tube (Fixed) **Function:**

Physical & Mechanical Properties

100.0 **Extension Length (mm):**

103.45	Total Length (mm):
37.0	Clear Aperture CA (mm):
48.0	Outer Diameter (mm):

Threading & Mounting

T-Mount	Thread Type:
---------	---------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

;