

100X DIN Semi-Plan, Finite Intl Standard Objective



Stock #33-472 3-5 DAYS

- 1 + **A\$395.20**

ADD TO CART

Qty 1+
A\$395.20

Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm):
546

Field of View (mm):
0.2

Focal Length FL (mm):
1.60

Length excluding Threads (mm):
44.80

Magnification:
100X

Maximum Diameter (mm): 25
Numerical Aperture NA: 1.25
Mounting Threads: RMS / 20.32mm x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 160mm
Type: Semi-Plan
Depth of Field (µm): 0.65
Field of View, 18 Diameter Field Eyepiece (mm): 0.18
Operating Temperature (°C): +10 to +40
Operating Humidity: Max 85% at 35°C with no condensation
Working Distance (mm): 0.22
Weight (g): 88.2
Note: Recommended Immersion Oil #86-834
Wavelength Range (nm): 400 - 700
Style: Finite Conjugate
Field Number (mm): 20
Parfocal Length (mm): 45.02
Immersion Liquid: Oil

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View