

105mm Dia x 145mm FL Cold Mirror Coated, Ellipsoidal Reflector



Precision Ellipsoidal Reflectors

Stock #90-974 3-5 DAYS

-

1

+

A\$776.00

ADD TO CART

Qty 1-10

A\$776.00

Qty 11+

A\$682.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Substrate:  BOROFLOAT®

Coating:
Cold Mirror, 0°

Coating Type:
Metal

Center Hole Diameter (mm):

27.0
Height (mm): 42.0
Inner Diameter (mm): 99
Outer Diameter (mm): 105.00 +0.0/-0.5
Type: Specialty Mirror
Distance to Focal Point f_1 (mm) : 22
Distance to Focal Point f_2 (mm): 145

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
