

# 1064nm Flat Top Beam Shaper | πShaper 12\_12\_1064\_HP

See More by [AdlOptica](#)



Stock #15-495 [CONTACT US](#)

⊖ 1 ⊕ **A\$13,456.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-4                       |
| A\$13,456.00                  |
| Qty 5+                        |
| A\$12,113.60                  |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

## Get Product Downloads

|                                                               |
|---------------------------------------------------------------|
| Design Wavelength DWL (nm):<br>1064                           |
| Diameter (mm):<br>42.00                                       |
| Entrance Beam Diameter, 1/e <sup>2</sup> (mm):<br>12.0 - 12.1 |
| Model Number:                                                 |

|                                                                                                     |
|-----------------------------------------------------------------------------------------------------|
| πShaper 12_12_1064_HP                                                                               |
| <b>Length (mm):</b><br>358.00                                                                       |
| <b>Mounting Threads:</b><br>M27 x 1                                                                 |
| <b>Type:</b><br>Beam Shaper                                                                         |
| <b>Weight (g):</b><br><530                                                                          |
| <b>Wavelength Range (nm):</b><br>1020 - 1100                                                        |
| <b>Style:</b><br>Flat Top                                                                           |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>3 J/cm <sup>2</sup> @ 5ns (typical) |
| <b>Output Diameter, FWHM (mm):</b><br>12.0                                                          |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |