

TECHSPEC® 10mm Aluminized, Half-Penta Prism



Stock **#65-587** 3-5 DAYS

- 1 + **A\$236.00**

ADD TO CART

Qty 1-5
A\$236.00
Qty 6+
A\$188.80
Volume Pricing
Request Quote

Get Product Downloads



Coating:
VS 0° & Aluminized

Substrate: ▢
[N-BK7](#)

Height (mm):
14.14

Surface Quality:

40-20
Type: Half-Penta Prism
Dimensional Tolerance (mm): ±0.10
Angle Tolerance (arcmin): ±3
Bevel: Protective bevel as needed
Image Orientation: Right-Handed
Coating Specification: Entrance/Exit Faces: R _{avg} ≤0.4% @ 425 - 675nm Reflecting Surface: R _{avg} >85% @ 400 - 700nm w/Black Overpaint
Ray Deviation (°): 45
Wavelength Range (nm): 425 - 675
Surface Flatness (P-V): λ/2
Width (mm): 10.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant