

TECHSPEC® 10mm Dia 0.50 NA, Uncoated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#87-974** 3-5 DAYS

[Other Coating Options](#)

− 1 +

A\$568.00

ADD TO CART

Qty 1-5

A\$568.00

Qty 6+

A\$454.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
10.00 +0.0/-0.1

Effective Focal Length EFL (mm):

10.00 @ 587.6nm
Numerical Aperture NA: 0.50
Back Focal Length BFL (mm): 5.89
Substrate: Fused Silica (Corning 7980)
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 8
Edge Thickness ET (mm): 2.77
Center Thickness CT (mm): 6.00 ±0.1
f/#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 200 - 2200
Conjugate Distance: Infinite
Power (diopters): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View