

TECHSPEC® 10mm Dia. x 1.5mm Thickness 1.65-3µm Coated Silicon Window



TECHSPEC Silicon (Si) Windows

Stock **#17-195** 3-5 DAYS

- 1 +

A\$216.00

ADD TO CART

Qty 1-10

A\$216.00

Qty 11+

A\$194.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture CA (mm):
9.00

Diameter (mm):
10.00 +0.0/-0.1

Thickness (mm): 1.50 ±0.1
Coating: BBAR (1650-3000nm)
Coating Specification: R _{avg} <1% @ 1650 - 3000nm R _{abs} <2% @ 1650 - 3000nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 2.55
Density (g/cm³): 2.33
Edges: Fine Ground
Index of Refraction n_d: 3.422 @ 5µm
Knoop Hardness (kg/mm²): 1150
Parallelism (arcmin): <3
Poisson's Ratio: 0.265
Substrate: Silicon (Si)
Surface Flatness (P-V): 1λ
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 1650 - 3000
Young's Modulus (GPa): 140

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant