

TECHSPEC® 10mm NIR, 30R/70T, Non-Polarizing Cube Beamsplitter



Stock #13-422 3-5 DAYS

- 1 + **A\$363.20**

ADD TO CART

Qty 1-5
A\$363.20
Qty 6+
A\$283.20
Volume Pricing
Request Quote

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating:

NIR
Coating Specification: R _{avg} <0.5% @ 720 - 1080nm
Construction: Cube
Dimensions (mm): 10.0 x 10.0 x 10.0 ±0.1
Reflection/Transmission Ratio (R/T): 30/70
Substrate:  N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 720 - 1080
[Ts-Tp]: <6%
Absolute Transmission (%): 65 ±10
Average Transmission (%): 65 ±5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View