

TECHSPEC® 10mm Sq., 1mm Thick, VIS-EXT Coated λ/4 N-BK7 Window



Stock **#23-457** 3-5 DAYS

- 1 + **A\$126.40**

ADD TO CART

Qty 1-5
A\$126.40
Qty 6+
A\$101.20
Volume Pricing
Request Quote

Get Product Downloads



Abbe Number (v_d):
64.17

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):

9.00 x 9.00
Dimensions (mm): 10.00 x 10.00 +0.00/-0.25
Thickness (mm): 1.00 ±0.20
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Fine Ground
Index of Refraction n_d: 1.516
Knoop Hardness (kg/mm²): 610
Parallelism (arcmin): <1
Poisson's Ratio: 0.206
Substrate: N-BK7
Surface Quality: 60-40
Transmitted Wavefront, P-V: λ/4
Type: Protective Window
Wavelength Range (nm): 350 - 700
Young's Modulus (GPa): 82
Length (mm): 10.00
Width (mm): 10.00
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant