

[See all 21 Products in Family](#)

TECHSPEC® 10mm TFL Mount Camera Lens Spacer



10mm TFL Mount Camera Lens Spacer



Stock #12-774 **20+ In Stock**

⊖ 1 ⊕ A\$64.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$64.80 each
Need More?	Request Quote

Product Downloads

General

Lens Accessory **Type:**

Physical & Mechanical Properties

14.0 **Total Length (mm):**

45.0 **Outer Diameter (mm):**

10.0

Extension Length (mm):

Threading & Mounting

TFL Mount

Mounting Threads:

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- APS-C (27.9mm), TFL-Mount Lens or M40 Mount Lens
- Greater than 30 MegaPixels, 3.45µm Pixel Size Sensors
- High Resolution, Compact APS-C Lens (CA)
- 35mm to 100mm Focal Length

TECHSPEC® CA (Compact APS) Series Fixed Focal Length Lenses are designed for high-resolution large-format sensors. Covering the APS-C format sensors with a 28mm image circle, these lenses feature a [TFL Mount](#) or M40 Mount. TFL Mounts feature an M35 x 0.75 thread with a 17.5mm flange distance, and offer the same robustness and ease of use as a C-Mount. M40 Mounts feature a M52 x 0.75 thread with a 17.526mm flange and provide a robust, large-format mounting solution ideal for high-resolution and larger image sensors with improved mechanical stability and optical performance compared to smaller format mounts. TECHSPEC® CA Series Fixed Focal Length Lenses offer a compact size while accommodating large format sensors, making them ideal for machine vision and [factory automation](#) applications.

These lenses won the [3rd place 2020 Inspect Award](#) and the [Silver-Level 2020 VSD Innovators Award](#).