

10mW, 532nm DPSS Pointing Laser



DPSS Pointing Lasers

Stock **#37-028** 3-5 DAYS

- 1 + **A\$572.00**

ADD TO CART

Qty 1-9
A\$572.00
Qty 10+
A\$515.20
Volume Pricing
Request Quote

Get Product Downloads



Operating Temperature (°C):
23 to 27

Operating Voltage (V):
5.0

Output Power (mW):
10

Spatial Mode:

TEM ₀₀
Wavelength (nm): 532.00 ±1
Wavelength Tolerance (nm): ±1
Power Supply: Power Supply Required and Sold Separately. USA: #83-855 Europe: #83-855 Japan: #13-640 Korea: #33-770 China: #83-855
Modulation Frequency (kHz): 0 - 10
Note: Compatible TEC Controller (#19-476) sold separately
Beam Diameter (mm): 1.0 Typical
Beam Divergence (mrad): <1 Typical
Laser Class - CDRH: IIIb
Color: Green
Length (mm): 90.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant