


10" x 12" Size, Plastic Optical Window



Stock **#46-629** 3-5 DAYS

- 1 + **A\$232.00**

ADD TO CART

Qty 1-49
A\$232.00
Qty 50+
A\$208.80
Volume Pricing
Request Quote

Get Product Downloads



Abbe Number (v_d):
57.00

Dimensions (mm):
254.00 x 304.80

Dimensions (inches):
10 x 12.00

Thickness (mm):

1.50 ±0.15
Coating: Uncoated
Density (g/cm³): 1.320
Index of Refraction n_d: 1.501
Operating Temperature (°C): 100 Continuous, 130 for 1 hour
Substrate: Thermoset ADC (CR-39®)
Transmission (%): >90 (typical)
Type: Protective Window
Wavelength Range (nm): 400 - 1500
Length (mm): 304.80
Width (mm): 254.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View