

10X (13 - 130mm FL) C-Mount, Close Focus Zoom lens



10X (13 - 130mm FL) C-Mount, Close Focus Zoom Lens, #54-363

Stock **#54-363** [CONTACT US](#)

⊖ 1 ⊕

A\$1,128.00

ADD TO CART

Qty 1+
A\$1,128.00

Volume Pricing
Request Quote

Get Product Downloads

Length (mm): 98.50
Horizontal Field of View, 1/2" Sensor: 7.8 - 280mm
Filter Thread: M46 x0.75
Maximum Diameter (mm): 48.00
Weight (g): 233.00

Note: Minimum: 0.82X - 0.085X Maximum: 0.23X - 0.023X
Zoom Ratio: 10:1
Type: Zoom Lens, Macro
Focal Length FL (mm): 13.00 - 130
Primary Magnification PMAG: 0.82X - 0.023X
Maximum Sensor Format: 1/2"
Working Distance (mm): 152 - 457
Mount: C-Mount
Aperture (f/#): f/5.6 - f/32
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View