

10X DIN Achromatic Commercial Grade Objective



Stock #43-903 3-5 DAYS

- 1 + **A\$160.00**

ADD TO CART

Qty 1+
A\$160.00

Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
17.13

Length excluding Threads (mm):
40.00

Magnification:
10X

Maximum Diameter (mm):
24

Numerical Aperture NA:
0.25

Mounting Threads: 0.7965-36 TPI, 55° Whitworth
Type: Achromatic
Operating Temperature (°C): 5 to 40
Storage Temperature (°C): -20 to 60
Working Distance (mm): 6.14
Style: Finite Conjugate
Parfocal Length (mm): 46.14
Immersion Liquid: N/A
Operating Relative Humidity: 45% to 85%

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
