

10X Objective, Nikon CFI Plan Fluor

See More by [Nikon](#)



10X Objective, Nikon CFI Plan Fluor, #88-379

Stock **#88-379** 3-5 DAYS

-

1

+

A\$1,619.20

ADD TO CART

Qty 1+

A\$1,619.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Field of View (mm):
2.5

Horizontal Field of View, 1/2" Sensor:
0.64mm

Horizontal Field of View, 2/3" Sensor:
0.88mm

Model Number:

MRH00105
Length excluding Threads (mm): 42.40
Magnification: 10X
Maximum Diameter (mm): 30
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.30
Mounting Threads: M25 x0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Working Distance (mm): 16.0
Weight (g): 150.00
Style: Infinity Corrected
Manufacturer: Nikon
Field Number (mm): 25
Parfocal Length (mm): 58.4
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View
