

80.5mm Max. Aperture, Iris Diaphragm



Stock #32-613 3-5 DAYS

- 1 + **A\$512.00**

ADD TO CART

Qty 1-4
A\$512.00
Qty 5+
A\$451.68
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
4.5

Maximum Aperture (mm):
80.5

Outer Diameter (mm):
110.0

Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 13.00
Number of Leaves: 16.00
Thickness (mm): 10.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)