

117mm Outer Dia., Zero Aperture, Stainless Steel Leaves



Zero Series

Stock #57-600 3-5 DAYS

- 1 +

A\$528.00

ADD TO CART

Qty 1-4

A\$528.00

Qty 5+

A\$466.08

Volume Pricing

[Request Quote](#)

Get Product Downloads

Minimum Aperture (mm):
0.00

Maximum Aperture (mm):
75.0

Outer Diameter (mm):
117.0

Construction:

Anodized Aluminum Alloy, Stainless Steel Leaves

Full Angular Range of Lever (°):
97.00

Lever Length (mm):
53.00

Lever Position (mm):
4.8

Lever Size (mm):
15.00 x 5.00

Number of Leaves:
Two sets of 9

Operating Temperature (°C):
<400

Pin Thread & Pitch:
N/A

Thickness (mm):
9.50

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)