

# 300 x 300mm, 0.10mm FL, Lenticular Array



Stock **#22-726** CLEARANCE 3-5 DAYS

- 1 +

**A\$299.12**

ADD TO CART

|           |
|-----------|
| Qty 1+    |
| A\$299.12 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

## Get Product Downloads

Effective Focal Length EFL (mm):  
0.10

Substrate: ☐  
Acrylic

Coating:  
Uncoated

Type:  
Lens Array

Wavelength Range (nm):  
400 - 1600

|                                                      |
|------------------------------------------------------|
| <b>Center Thickness CT (mm):</b><br>2.00             |
| <b>Dimensional Tolerance (mm):</b><br>±0.5           |
| <b>Dimensions (inches):</b><br>11.811 x 11.811       |
| <b>Dimensions (mm):</b><br>300 x 300                 |
| <b>Effective Focal Length EFL (inches):</b><br>0.004 |
| <b>Effective Size (inches):</b><br>11.811 x 11.811   |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.49 |
| <b>Note:</b><br>Warpage Tolerance of ±3mm            |
| <b>Number of Lenses:</b><br>363 per 25.4mm           |
| <b>Operating Temperature (°C):</b><br>60 (Maximum)   |
| <b>Thickness Tolerance (mm):</b><br>±0.1             |
| <b>Effective Size (mm):</b><br>300 x 300             |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |