

1.2 OD M40.5 x 0.50, Machine Vision Absorptive ND Filter



Stock #21-668 3-5 DAYS

- 1 + **A\$108.00**

ADD TO CART

Qty 1-9
A\$108.00
Qty 10+
A\$103.68
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
1.2

Clear Aperture CA (mm):
35.50

Filter Thread:
M40.5 x 0.50

Substrate: ☐
ND Filter Glass

Surface Quality: 40-20
Transmission (%): 6.25
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
