

12", Red 625nm, UltraSeal Washdown Bar Light

See More by [Advanced Illumination](#)



Advanced Illumination UltraSeal Washdown Bar Lights

Stock **#18-630** 3-5 DAYS

1

A\$2,099.20

ADD TO CART

Qty 1+

A\$2,099.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Color:
Red

Input Voltage (V):
24V

Model Number:
AL247M12-625IC

Operating Temperature (°C):
0 - 60

Dimensions (mm):

323.8 x 42.9 x 24
Wavelength (nm): 625.00
Weight (g): 657
LED Lifetime (hours): 50000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Area Light
Illumination Mode: Constant
Environmental Rating: IP69K
Minimum Input Current: 0.60A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)