

1200 Grooves/mm, 50mm Sq, UV Transmission Grating Beamsplitter



Stock #85-300 3-5 DAYS

-

1

+

A\$528.00

ADD TO CART

Qty 1-9

A\$528.00

Qty 10+

A\$475.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Groove Density (grooves/mm):
1200

Wavelength Range (nm):
250 - 450

Blaze Angle (°):
26.7

Dimensions (mm): 50.00 x 50.00
Construction: Blazed Grating
Length (mm): 50.00
Substrate: ☐ Fused Silica (Corning 7980)
Thickness (mm): 2.00 ±0.5
Type: Transmission Diffraction Grating
Width (mm): 50.00
Alignment of Grooves to Edge (°): ±0.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
