

12.0mm FL, IR-Cut Filter at 650nm, f/2, Micro Video Lens



Stock **#66-893** 3-5 DAYS

[Similar Products](#)

- 1 +

A\$94.40

ADD TO CART

Qty 1-49
A\$94.40
Qty 50+
A\$75.20
Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
12.10

Filter Thread:
M12 x0.50

Maximum Diameter (mm):
14.0

Maximum Image Circle (mm):

6.00
Horizontal Field of View @ Max Sensor Format: 22.2
Resolution, On-Axis: 63 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 60 lp/mm @ 20% Contrast
Resolution, Full Field: 60 lp/mm @ 20% Contrast
Note: IR Cut-Off Filter Included
Type: M12 Imaging Lens
Focal Length FL (mm): 12.00
Maximum Sensor Format: 1/3"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2
Distortion (%): -0.15 @ Full Field
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View
