

90mm Max. Aperture, Iris Diaphragm



Stock #32-612 3-5 DAYS

- 1 + **A\$593.60**

ADD TO CART

Qty 1-4
A\$593.60
Qty 5+
A\$523.52
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
5.0

Maximum Aperture (mm):
90.0

Outer Diameter (mm):
120.0

Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 13.40
Number of Leaves: 20.00
Thickness (mm): 12.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)