

[See all 2 Products in Family](#)

(12.5-75mm FL), 6X Manual Zoom Video Lens



#53-153

Stock **#53-153** [CONTACT US](#)

-

1

+

A\$1,016⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,016.00 each
Need More?	Request Quote

Product Downloads

General	
Macro Zoom Lens	Type:
Physical & Mechanical Properties	
114.50	Length (mm):
57.00	Maximum Diameter (mm):
475.00	Weight (g):

Optical Properties	
495 - 86	Field of View @ Min Working Distance (mm):
27.8° - 4.9°	Horizontal Field of View, 1/2" Sensor:
6:1	Zoom Ratio:
12.5-75	Focal Length Range (mm):
1,000 - ∞	Working Distance (mm):
f/1.2 - f/16	Aperture (f/#):
VIS	Lens Wavelength Range:

Sensor

2/3"	Maximum Sensor Format:
------	------------------------

Threading & Mounting

M55.0 x 0.75	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Manual Zoom, Focus and Iris Control
- Features Locking Set Screws
- C-Mount

Manual Zoom Imaging Lenses provide manual adjustment of focal length (zoom), iris, and focus. Zoom lenses cover the focal length range of several fixed focal length lenses in one lens. Manual Zoom Imaging Lenses should be used when a variable angle field of view is required. Ideal applications include inspection, machine vision, and robotics.

Technical Information

