

TECHSPEC®

12.5" Diameter x 75" FL Uncoated, Parabolic Mirror



Stock #32-276-000

3-5 DAYS

-

1

+

A\$4,584.00

ADD TO CART

Qty 1-2
A\$4,584.00
Qty 3+
A\$3,896.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate:

BOROLOAT®

SUPREMAX®

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 12.5 +0.06/-0
Diameter (mm): 317.50 +1.5/-0
Effective Focal Length EFL (inches): 75.0
Effective Focal Length EFL (mm): 1,905.00
Radius of Curvature (mm): 3,810.00
Aperture (f/#): f/6
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Clear Aperture CA (mm): 286
Edge Thickness ET (inches): 2.13
Edge Thickness ET (mm): 54.10
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View