

TECHSPEC® 125mm, Center Drive, Standard Top, Metric Stage



TECHSPEC® Crossed-Roller Bearing Linear Translation Stages (Standard-Top Model)



Stock #66-456 3-5 DAYS

1

A\$878.40

ADD TO CART

Qty 1-2

A\$878.40

Qty 3+

A\$766.72

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:

Lead Screw
Drive Orientation: Center Drive
Type: Metric
Stage Size (mm): 125 x 125
Travel (mm): 25
Center Hole: M6 x 1
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 20
Mounting Threads: (21) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4
Stage Size (inches): 4.92 x 4.92
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant