

12.5mm Dia. Left-Handed Plastic Circular Polarizer (CP42HE)



Stock **#88-095** 3-5 DAYS

- 1 +

A\$35.20

ADD TO CART

Qty 1-5
A\$35.20
Qty 6+
A\$28.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Substrate: ☐
[CP42HE on PMMA](#)

Operating Temperature (°C):
-40 to +80

Thickness (mm):
2.29 ±0.24

Transmission (%) : 42
Type : Left-Handed Circular Polarizer
Dimensional Tolerance (mm) : +0.0/-0.3
Construction : Polarizing Film on PMMA
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.90
Heat Resistance (°C x Hours) : 80 x 500
#Sorting : 1.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant