

125mm Dia x 250mm Focal Length, MgF₂ Coated, PCX Condenser Lens



Stock #19-908 3-5 DAYS

-

1

+

A\$342.40

ADD TO CART

Qty 1-10
A\$342.40
Qty 11+
A\$308.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
125.00 +0.0/-0.5

Effective Focal Length EFL (mm):
250.00 @ 587.6nm

Back Focal Length BFL (mm):
237.00

Coating:
MgF₂ (400-700nm)

Coating Specification: R_{avg} ≤1.75% @400 - 700nm
Substrate: N-BK7
Surface Quality: 120-80
Center Thickness CT (mm): 20.00
Edge Thickness ET (mm): 3.88
Radius R₁ (mm): 129.20
Clear Aperture CA (mm): 122
f#: 2.00
Numerical Aperture NA: 0.25
Type: Condenser Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
