

TECHSPEC® 12.5mm Dia x 25mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #46-194

3-5 DAYS

-

1

+

A\$99.20

ADD TO CART

Qty 1-5

A\$99.20

Qty 6+

A\$79.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50

Effective Focal Length EFL (mm):
25.00

Substrate:

N-BK7

f/#:

Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 23.09
Center Thickness CT (mm): 2.90
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.29
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 12.96
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
