

12.5mm Diameter 120 Grit Ground Glass Diffuser



Stock **#83-418** 3-5 DAYS

- 1 +

A\$19.60

ADD TO CART

Qty 1-10
A\$19.60
Qty 11+
A\$18.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50 ±0.25

Coating:
Uncoated

Edges:
Ground Edges

Grit: ☐
120

Substrate: Float Glass
Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 350 - 2000
Note: Sandblasted on first surface

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant